# **EURO**QUARTZ

# X42-W CRYSTALS

**WI-FI APPLICATIONS** 

## 4 x 2.5 x 0.6mm SMD

#### **FEATURES**

- Miniature package: 4.0 x 2.5 x 0.6mm
- Gold-plated ceramic base with metal seam-welded package
- Very low ageing
- Optimized for Wi-Fi applications
- High shock and vibration resistance

### DESCRIPTION

X42 crystals are micro-miniature surface-mount mount crystals. The crystals have a gold plated ceramic base with a seam welded metal lid providing a stable crystal with very low ageing. The rugged construction ensures that this crystal has high shock and vibration resistance. The crystal has been optimized for WI-Fi applications: Bluetooth/ Bluetooth Low Energy (BLE), Bluetooth Smart, Zigbee, ISM, Wi-FI / WLAN, LPWAN and others.

### **SPECIFICATION**

Standard Frequencies*:	16.0, 19.2, 20.0, 24.0, 25.0, 26.0, 27.120, 30.0, 32.0, 37.40, 38.40, 40.0, 48.0, 52.0MHz	
Operating Mode:	AT-Cut Fundamental:	
Calibration Tolerance at 25°C:	±10ppm	
Frequency stability		
-20° to +70°C	±10ppm	
-40° to +85°C	±15ppm	
-40° to +105°C	±30ppm	
Storage Temperature:	-50°~+105°C	
Equivalent Series Resistance:	See table	
Shunt Capacitance (C0):	2pF to 4pF typical, 5pF maximum	
Load Capacitance (CL):	Series or from 10pF to 32pF	
	(Customer specified CL)	
Ageing:	<±ppm per first year at +25°C	
Drive level:	100 $\mu$ W maximum	
Reflow Soldering:	10s maximum at 260°C twice	
	or 180s at 230°C, once.	
Packaging:	12mm EIA tape and reel	

ıyı пy

\*Note: Custom frequencies are available.

### **EQUIVALENT SERIES RESISTANCE (ESR)**

Frequency Range MHz	Crystal Cut/ Mode	ESR Ω Max.
12.0 ~ 14.9	AT Fund.	80
15.0 ~ 29.9	AT Fund.	50
30.0 ~ 54.0	AT Fund.	40


### **ENVIRONMENTAL PERFORMANCE**

Compliant
-55° to +105°C
85% RH, 85°C for 48 hours
Leak rate 2x10-8 ATM -cm³/s max.
MIL-STD-202F Method 208E
260°C for 10 sec (see diagram)
MIL-STD-202F Method 204,
35±5 mins, 50 to 2000Hz
MIL-STD-202F Method 213B, test
Condition E, 50g 11ms.






#### **OUTLINE & DIMENSIONS**



\* Note: These parts may be supplied with the chamfered pad in different positions. However, the crystal connection is always as shown above.

#### PART NUMBER GENERATION

Part numbers for X42-W crystals are generated as follows:



(Either SR for series or CL in pF)